

3.0 OD M43 x 0.75, Machine Vision Absorptive ND Filter



Stock **#21-704** ☐ In Stock

-

1

+

C\$166.60

ADD TO CART

Qty 1-9
C\$166.60
Qty 10+
C\$158.76
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
3.0

Clear Aperture CA (mm):
38.00

Filter Thread:
M43 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%) : 0.10
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
