

300 Grooves, 25mm Sq, 17.5° Groove Angle Grating



Stock **#49-579** ☐ In Stock

-

1

+

C\$168.00

ADD TO CART

Qty 1-9

C\$168.00

Qty 10+

C\$151.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
300

Wavelength Range (nm):
400 - 700

Blaze Angle (°):
17.5

Dimensions (mm): 25.00 x25.00
Construction: Blazed (Ruled) Grating
Length (mm): 25.00
Substrate: ☐ B270
Thickness (mm): 3.00 ±0.5
Type: Transmission Diffraction Grating
Wavelength: VIS
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5
Groove Angle (°): 17.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
