

300 Grooves, 50mm Sq, 17.5° Groove Angle Grating



Stock **#49-583** ☐ In Stock

- 1 + **C\$315.00**

ADD TO CART

Qty 1-9
C\$315.00
Qty 10+
C\$283.50
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
300

Wavelength Range (nm):
400 - 700

Blaze Angle (°):
17.5

Dimensions (mm): 50.00 x 50.00
Construction: Blazed (Ruled) Grating
Length (mm): 50.00
Substrate: ☐ B270
Thickness (mm): 3.00 ±0.5
Type: Transmission Diffraction Grating
Wavelength: VIS
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5
Groove Angle (°): 17.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
