

300 Grooves/mm, 12.7mm Sq, UV Transmission Grating Beamsplitter



Stock #85-287 ☐ In Stock

-

1

+

C\$161.00

ADD TO CART

Qty 1-9
C\$161.00
Qty 10+
C\$144.90
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
300

Wavelength Range (nm):
250 - 500

Blaze Angle (°):
8.6

Dimensions (mm): 12.70 x 12.70
Construction: Blazed Grating
Length (mm): 12.70
Substrate:  Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
