

300 Grooves/mm, 50mm Sq, UV Transmission Grating Beamsplitter



Stock #85-296

CONTACT US

-

1

+

C\$462.00

ADD TO CART

Qty 1-9
C\$462.00
Qty 10+
C\$415.80
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):

300

Wavelength Range (nm):

250 - 500

Blaze Angle (°):

8.6

Dimensions (mm): 50.00 x 50.00
Construction: Blazed Grating
Length (mm): 50.00
Substrate:  Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View