

## 300 x 300mm Left-Handed Plastic Circular Polarizer (CP42HE)



Stock #14-356 CLEARANCE ☐ In Stock

-

1

+

C\$264.53

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| C\$264.53 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

Substrate: ☐  
[Polymer Film CP42HE](#)

Length (mm):  
300.00

Operating Temperature (°C):  
-40 to +80

Dimensions (mm):  
300.0 x 300.0

Thickness (mm):  
0.27 ±0.04

|                                                 |
|-------------------------------------------------|
| <b>Thickness Tolerance (mm):</b><br>±0.03       |
| <b>Transmission (%):</b><br>42                  |
| <b>Type:</b><br>Left-Handed Circular Polarizer  |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-3.0 |
| <b>Construction:</b><br>Polarizing Film         |
| <b>Wavelength Range (nm):</b><br>400 - 700      |
| <b>Polarization Efficiency (%):</b><br>>99.90   |
| <b>Width (mm):</b><br>300.00                    |
| <b>#Sorting:</b><br>31.00                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Contains SVHC(s)</a>      |