



300 x 300mm, $\lambda/2$ Retarder Film (WP280)



Retarder Film with protective film removed



Stock **#88-256** ☐ In Stock

1

C\$208.60

ADD TO CART

Qty 1-10
C\$208.60
Qty 11+
C\$183.40
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
560

Substrate: ☐
[Polymer Film WP280](#)

Length (mm):

300.00
Operating Temperature (°C): -30 to +80
Retardance: λ/2
Dimensions (mm): 300.0 x 300.0
Thickness (mm): 0.06 ±0.006
Transmission (%): >90
Type: Retarder Film
Dimensional Tolerance (mm): +0.0/-2.0
Construction: Polarizing Film
Phase Shift (°): 180.00
Haze (%): <1
Note: Fast axis is indicated by a black stripe on the protective film. This film should be removed before use.
Wavelength Range (nm): 400 - 700
Heat Resistance (°C x Hours): 80 x 1000
Width (mm): 300.00
Retardation (nm): 280 ±5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
