

TECHSPEC® 300 x 300mm Linear Plastic Polarizer (XP42-200)



Stock **#86-199** ☐ In Stock

-

1

+

C\$308.00

ADD TO CART

Qty 1-5
C\$308.00
Qty 6+
C\$245.00
Volume Pricing
Request Quote

Get Product Downloads

Extinction Ratio:
9000:1

Substrate: ☐
[XP42-200 on PMMA](#)

Length (mm):
300.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm): 300.0 x 300.0 +0.0/-2.0
Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98
Width (mm): 300.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant