

TECHSPEC®

30.0mm Dia. x 30.0mm FL, Uncoated, Plano-Convex Lens



Stock **#48-653** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$53.90

ADD TO CART

Qty 1-9
C\$53.90
Qty 10+
C\$48.65
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Back Focal Length BFL (mm): 26.13
Coating: Uncoated
Substrate:  N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.90 ±0.10
Edge Thickness ET (mm): 1.5
Radius R₁ (mm): 23.54
Clear Aperture CA (mm): 29
f#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View