

300mm Dia x 42mm FL Alum. Coated, Parabolic Reflector



Stock **#90-966** ☐ In Stock

-

1

+

C\$1,954.40

ADD TO CART

Qty 1-10
C\$1,954.40
Qty 11+
C\$1,722.70
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Diameter (mm):
300.00 +0.0/-0.5

Focal Length FL (mm):
42.00

Aperture (f#):
0.140

Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @400 - 700nm
Coating Type: Metal
Center Hole Diameter (mm): No Center Hole
Height (mm): 130.0
Type: Parabolic Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View