

[All Products](#) / [Optics](#) / [Fiber Optics](#) / [Fiber Optic Image Conduits](#)

[See all 20 Products in Family](#)

304.8mm Standard Res Image Conduit with 100µm Fibers



Stock **#38-308** ☐ In Stock

-

1

+

C\$662.20

ADD TO CART

Qty 1-4
C\$662.20
Qty 5+
C\$595.98
Volume Pricing
Request Quote

Get Product Downloads

Minimum Bend Radius (mm):
25.6

Diameter Tolerance (inches):
±0.010

Length (mm):
304.80

Numerical Aperture NA:
0.53

Number of Fibers: 3012.00
Operating Temperature (°C): 454.00
Outer Diameter (mm): 6.40
Resolution: 5 lp/mm
Transformation Temperature (°C): 704.00
Transmission (%): 35 - 45
Fiber Diameter (µm): 100.00
Type: Standard Resolution
Length Tolerance (inches): ±0.030
Packing Fraction (%): 100.00
Index of Refraction n_d - Core: 1.58
Index of Refraction n_d - Cladding: 1.49
Wavelength Range (nm): 350 - 1500

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View