

30° Diffusing Angle 12.5mm Unmounted



Stock **#35-867** ☐ In Stock

1 **C\$126.00**

ADD TO CART

Qty 1-5
C\$126.00
Qty 6+
C\$94.50
Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°): ±3
Diffusing Angle (°): 30 (FWHM)
Diameter (mm): 12.50
Dimensional Tolerance (mm): ±0.5

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant