

30mm Aperture, Acktar Blackened Laser Beam Trap

See More by [Acktar](#)



Acktar Blackened Laser Beam Trap



Stock **#13-515** ☐ In Stock

1

C\$334.60

ADD TO CART

Qty 1-2
C\$334.60
Qty 3+
C\$315.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Laser Beam Trap

Construction:
Black Anodized Aluminum

Aperture Size: 30mm (Dia.)
Coating: Vacuum Black & Metal Velvet
Length (mm): 70.00
Outer Diameter (mm): 41.5
Mount Diameter (mm): 55
Mounting Threads: M6 x 1.0
Model Number: LBD-T-30
Maximum Incident Power Density (W/cm²): 20
Maximum Power (W): 20
Wavelength Range (nm): 100 - 10000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant