

**TECHSPEC® 30mm Barrel for 25.0mm Dia. Achromats**



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#54-514** **20+ In Stock**

1  C\$88<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$88.90 each
Qty 6-25	C\$71.40 each
Qty 26-49	C\$70.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Physical & Mechanical Properties**

**Housing Diameter (mm):**  
30 +0.0/-0.10

**Housing Length (mm):**  
34 ±0.2

**Lens Edge Spacing at Mount (mm):**  
8

## Product Details

- 15mm and 30mm Diameter Options
- AR Coated Lenses
- Mounted Achromatic Pairs Kits Available

TECHSPEC® Mounted Achromatic Lens Pairs combine popular TECHSPEC® Achromats into common configurations used for relay and projection applications. Packaged in slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. 15.0mm pairs can be coupled into C-mount components using [Helicoid Barrel Accessory](#). TECHSPEC Mounted Achromatic Lens Pairs have also been oriented for optimum system performance. All lenses, 15.0mm and 30.0mm, are AR coated. Lower  $f\#$  pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

## Technical Information

