

TECHSPEC® 30mm, Center Drive, Thru-Hole, 0.25" Travel, Metric Micrometer



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Thru-Hole Model)



Stock **#83-509** ☐ In Stock

1

C\$548.80

ADD TO CART

Qty 1-2

C\$548.80

Qty 3+

C\$479.22

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:

Metric Micrometer
Drive Orientation: Center Drive
Type: Metric
Stage Size (mm): 30 x 30
Travel (mm): 6.5
Center Hole: 5/16"-24
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) 5/16"-24, (6) M2 x 0.4
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)