

TECHSPEC[®] 30mm, Center Drive, Thru-Hole, 0.5" Travel, English Stage



30mm, Center Drive, Thru-Hole, 0.5" Travel Stage

Stock #66-394 ☐ In Stock



1



C\$450.80

ADD TO CART

Qty 1-2

C\$450.80

Qty 3+

C\$393.26

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Crossed Roller Bearing

Type of Drive:

Lead Screw

Drive Orientation:

Center Drive
Type: English
Stage Size (mm): 30 x 30
Travel (inches): 0.5
Center Hole: 5/16"-24
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) 5/16"-24, (6) 2-56
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
