

TECHSPEC® 30mm Dia., Enhanced Deep UV (DUV) Mirror



Precision Ultraviolet Mirrors

Stock **#18-745** ☐ In Stock



1



C\$434.00

ADD TO CART

Qty 1-5

C\$434.00

Qty 6+

C\$347.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.2

Surface Flatness (P-V):
λ/10

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface: Commercial Polish
Surface Quality: 10-5
Coating Specification: R _{avg} ≥92% @ 190 - 250nm R _{avg} ≥83% @ 250 - 900nm
Coating: Enhanced Aluminum (190-900nm)
Coating Type: Metal
Angle of Incidence (°): 0
Clear Aperture (%): 90
Design Wavelength DWL (nm): 190
Parallelism (arcsec): <30
Thickness (mm): 5.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 190 - 900
Vacuum Compatibility: 10 ⁻⁷ Torr

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View