

TECHSPEC® 30mm Dia x 60mm FL, VIS-EXT, Inked, Double-Convex Lens



Stock **#89-189-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$95.20

ADD TO CART

Qty 1-9
C\$95.20
Qty 10+
C\$85.75
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
30.00 ±0.025

Back Focal Length BFL (mm):
58.33

Effective Focal Length EFL (mm):

60.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.26
Radius R₁=R₂ (mm): 61.15
Clear Aperture CA (mm): 29.00
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View