

**TECHSPEC® 3.0mm Diameter x 10.0mm Length, N-BK7 Rod Lens**



Stock **#45-940** **20+ In Stock**

- 1 + C\$78<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$78.40 each
Qty 6-25	C\$63.00 each
Qty 26-49	C\$58.80 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Rod Lens **Type:**

**Physical & Mechanical Properties**

3.00 +0.00/-0.03 **Diameter (mm):**

10.00 **Length (mm):**

+0/-0.1      Length Tolerance (mm):

## Optical Properties

**N-BK7**      Substrate:

Uncoated      Coating:

350 - 2200      Wavelength Range (nm):

40-20      Surface Quality:

## Regulatory Compliance

**Compliant**      RoHS 2015:

**Compliant**      Reach 224:

**View**      Certificate of Conformance:

## Product Details

- Focuses Collimated Light into a Line
  - Available in Diameters as Small as 1mm
- TECHSPEC® Rod Lenses are polished on the circumference and ground on both ends. Optical performance is similar to a cylinder lens. Collimated light passing through the diameter of the rod lens will be focused into a line. TECHSPEC® Rod Lenses are offered in diameters ranging from 1mm to 10mm.

## Technical Information

### Rod Lens

