

TECHSPEC[®] 3.0mm Diameter x 10.0mm Length, N-BK7 Rod Lens



Stock **#45-940** 20+ In Stock

-

1

+

C\$78⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$78.40 each
Qty 6-25	C\$63.00 each
Qty 26-49	C\$58.80 each
Need More?	Request Quote

Product Downloads

General	
Rod Lens	Type:
Physical & Mechanical Properties	
3.00 +0.00/-0.03	Diameter (mm):
10.00	Length (mm):

Length Tolerance (mm):		+0/-0.1
Optical Properties		
N-BK7	Substrate: ☐	
	Coating:	
Uncoated		
Wavelength Range (nm):		350 - 2200
Surface Quality:		40-20
Regulatory Compliance		
RoHS 2015:		Compliant
REACH 224:		Compliant
Certificate of Conformance:		View

Product Details

- Focuses Collimated Light into a Line
 - Available in Diameters as Small as 1mm
- TECHSPEC® Rod Lenses are polished on the circumference and ground on both ends. Optical performance is similar to a cylinder lens. Collimated light passing through the diameter of the rod lens will be focused into a line. TECHSPEC® Rod Lenses are offered in diameters ranging from 1mm to 10mm.

Technical Information

Rod Lens

