

30mm Length Post Set



Stock **#62-890** **1 In Stock**

-

1

+

C\$130²⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$130.20 each
Need More?	Request Quote

General	
Metric	Type:
Post Set	Note:

Physical & Mechanical Properties	
50	Total Fixed Height Adjustment (mm):
4 x 80	Weight (g):
30.00	Length (mm):
20.00	Diameter (mm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Large 200mm x 120mm Size Plate Set
- 20mm Diameter Stainless Steel Posts with Male and Female M6 Threads
- Use with Lab Jacks to Extend Working Surface

Our Height Adjustment Platforms are ideal for adjusting the height of an optical system. A complete system requires the Plate Set (Stock [#62-889](#)) and one of the four available Post Sets. The Plate Set includes one top plate and one bottom plate. The top plate contains (35) M4 x 0.7mm tapped holes spaced 25mm apart. The Post Sets includes (4) 20mm Diameter Posts, (4) M6 S.H.C.S, and an Allen Wrench. Posts have Male and Female M6 Threads. Post Sets of 30mm, 80mm, 130mm, and 180mm Lengths are available to create a fixed height adjustment.

Technical Information

