

TECHSPEC® 30mm N-SF11 MgF₂ Coated Equilateral Prism



Equilateral Prisms

Stock #47-283 In Stock

⊖ 1 ⊕

C\$242.20

ADD TO CART

Qty 1-5

C\$242.20

Qty 6+

C\$217.98

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
MgF₂ (400-700nm)

Length of Face (mm):
30.00

Substrate:
[N-SF11](#)

Length (mm):
30.00

Surface Quality:
40-20

Type:
Equilateral Prism

Dimensional Tolerance (mm):
 ± 0.1

Angle Tolerance (arcmin):
 ± 2

Image Orientation:
Dispersion

Coating Specification:
 $R_{avg} \leq 1.75\%$ @ 400 - 700nm

Wavelength Range (nm):
400 - 700

Power (fringes) @ 632.8nm:
2.50

Irregularity (fringes) @ 632.8nm:
0.50

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
