

TECHSPEC® 30mm, Side Drive, Standard Top, 0.25" Travel, Metric Micrometer



Stock **#83-506** ☐ In Stock

-

1

+

C\$506.80

ADD TO CART

Qty 1-2

C\$506.80

Qty 3+

C\$441.98

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Metric Micrometer

Drive Orientation: Side Drive
Type: Metric
Stage Size (mm): 30 x 30
Travel (mm): 6.5
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) M6 x 1, (6) M2 x 0.4
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)