

TECHSPEC®

30mm, Uncoated, N-BK7 High Tolerance RA Prism



N-BK7 High Tolerance Right Angle Prisms

Stock **#32-551** ☒ In Stock



1



C\$180.60

ADD TO CART

Qty 1-5

C\$180.60

Qty 6+

C\$144.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (arcsec):

±15

Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Surface Quality:

40-20
Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 42.40
Length of Legs (mm): 30.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View