

30mm X&Y, 40mm Z Travel, X-Y-Z Axis Rack & Pinion Stage



X-Y-Z Axis Metric Stages

Stock **#62-041** [CONTACT US](#)

-

1

+

C\$1,393⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$1,393.00 each
Qty 10+	C\$1,229.76 each
Need More?	Request Quote

Product Downloads

General

Metric

Type:

With locking lever

Note:

Physical & Mechanical Properties

Linear (X-Y-Z)

Type of Movement:

Guide System:

Dovetail	
40 x 34	Stage Size (mm):
30 (±15) in X and Y 40 (±20) in Z	Travel (mm):
None	Center Hole:
Rack and Pinion: Brass Stage: Aluminum	Construction:
1.5	Load Capacity (kg):
20	Travel Per Knob Rotation (mm):
0.63	Weight (kg):
0.1	Resolution (mm):

Hardware & Interface Connectivity

Type of Drive:	
Rack and Pinion	

Threading & Mounting

Mounting Threads:	
(8) M3 x 0.5	

Regulatory Compliance

RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	
Reach 247:	
Contains SVHC(s)	

Product Details

Use 120mm x 70mm Metric Base Plate ([#54-977](#)) to connect Rack and Pinion Stages to breadboards. Z Axis Right Angle Brackets are available for use with stages that support Z axis translation.

- Aluminum Stage with Brass Rack and Pinion
- 20mm Travel per Knob Rotation
- Scale Features 1mm Increments with Locking Lever
- [Basic Rack and Pinion Stages](#) Also Available

Rack and Pinion Stages are ideal for a wide range of applications requiring high load capacity, accuracy, and long travel distances. The knob provides coarse positioning adjustment with 20mm of travel per rotation and can be locked in place with the locking lever. These stages feature a Vernier scale with a resolution of 1mm for accurate and repeatable adjustments. Rack and Pinion Stages are available in a variety of translation axes, including Linear (X), Linear (X-Y), Linear (X-Z), Linear (X-Y-Z), and Linear (Z).

Note: Use 120mm x 70mm Metric Base Plate ([#54-977](#)) to connect Rack and Pinion Stages to breadboards. Z Axis Right Angle Brackets are available for use with stages that support Z axis translation.

Technical Information

