

31 x 77mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#32-366** ☐ In Stock

1

C\$34.30

ADD TO CART

Qty 1-5

C\$34.30

Qty 6+

C\$27.30

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm):

31.0 x 77.0 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 3.20
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 77.00
Width (mm): 31.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant