

## 3.25" x 4.00", 3.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock #46-113 **20+ In Stock**

⊖ 1 ⊕ C\$98<sup>70</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	C\$98.70 each
Qty 11-49	C\$88.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Fresnel Lens **Type:**

**Physical & Mechanical Properties**

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

**Dimensions (inches):**

3.25 x 4.0

**Dimensions (mm):**

82.55 x 101.6

**Effective Size (inches):**

3.0 x 4.0

**Thickness Tolerance (inches):**

±0.020

**Optical Properties**

**Effective Focal Length EFL (mm):**

76.20

**Substrate:**

Acrylic

**Coating:**

Uncoated

**Wavelength Range (nm):**

400 - 1100

**Effective Focal Length EFL (inches):**

3.00

**Groove Density (grooves/inch):**

80.00

**Index of Refraction (n<sub>d</sub>):**

1.49

**Transmission (%):**

85 (Typical)

**Environmental & Durability Factors**

**Operating Temperature (°C):**

80 (Maximum)

**Regulatory Compliance**

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 242:**

[Compliant](#)

**Product Details**

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

**Technical Information**

