

34mm Diameter, Prism Mount Metric



Stock #55-012 **20+ In Stock**

⊖ 1 ⊕ C\$589⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | C\$589.40 each |
| Qty 5-25 | C\$530.46 each |
| Qty 26-49 | C\$501.34 each |
| Need More? | Request Quote |

Product Downloads

General

Adjustable - Rotary & Tip-Tilt

Type:

Cube/Prism

Type of Optics:

Physical & Mechanical Properties

±3

Fine Rotation (°):

±3 Fine Tilt Angle (°):

Threading & Mounting

20.0 Size of Compatible Optics (mm):

M6 x 1.0 Compatible Post:

Regulatory Compliance

[Exempt](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Contains SVHC\(s\)](#) Reach 247:

Product Details

- Precision Fine Movement
- Holds Prisms up to 30mm
- Black Anodized Aluminum
- [Posts](#) and [Post Holders](#) Required for Mounting

Metric Prism Mounts permit ±3° precision fine movement rotation and ±3° X-Y axes tilt control. These mounts feature durable black anodized aluminum construction and hold prisms up to 30mm. [Posts](#) and [post holders](#) are required for mounting to a breadboard.

Technical Information

| Mount Diameter A | Maximum Prism Size B | Base Height C | Maximum Total Mount Height D | Stock No. |
|------------------|----------------------|---------------|------------------------------|-------------------------|
| 34 | 20 | 30 | 76 | #55-012 |
| 50 | 30 | 45 | 102 | #55-013 |

