

34mm Diameter, UV Cut-Off Filter



Stock **#54-049** CLEARANCE ☐ In Stock

-

1

+

C\$20.93

ADD TO CART

Qty 1+

C\$20.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
34.00 +0.0/-0.2

Cut-On Wavelength (nm):
390.00

Glass/Filter Number:
L-39

Substrate: ☐
Hoya L-39

Operating Temperature (°C):
-15 to 70

Coating: AR Coating
Color: Clear, Green Tint
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >80 (avg)
Type: UV Cut-Off Filter
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View