

**TECHSPEC® 35mm - 60mm Length, T-Mount Fine Focus Tube**



Stock #52-300 **1 In Stock**

⊖ 1 ⊕ C\$176<sup>00</sup>

**ADD TO CART**

Volume Pricing

Qty 1-4	C\$176.40 each
Qty 5-9	C\$156.24 each
Qty 10-25	C\$144.34 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Fine Focus Tube **Type:**  
Extension Tube (Adjustable) **Function:**

**Physical & Mechanical Properties**

35.0 - 60.0 **Extension Length (mm):**

33.0 Clear Aperture CA (mm):

48.0 Outer Diameter (mm):

## Threading & Mounting

T-Mount Thread Type:

M33 x 0.5 Barrel Thread:

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 235:

## Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

**Note:** Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

## Technical Information

