

3.5 OD 50mm Sq., Absorptive ND Filter

See More by [Hoya](#)



Stock **#36-271** ☐ In Stock

- 1 +

C\$133.00

ADD TO CART

Qty 1-10
C\$133.00
Qty 11+
C\$117.60
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
3.5 ±0.2

Glass/Filter Number: Hoya ND-006
Substrate: ☐ ND Filter Glass
Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.531
Surface Quality: 80-50
Transformation Temperature (°C): 542.00
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 0.03 (average)
Type: Neutral Density Filter
Width (mm): 50.00
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.2
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View
