

35 x 35mm, 75R/25T, Plate Beamsplitter



Stock **#46-611** ☐ In Stock

- 1 +

C\$85.40

ADD TO CART

Qty 1-9
C\$85.40
Qty 10+
C\$64.40
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR 1/λ MgF₂ @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 35.0 x 35.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 75/25
Substrate: Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant