

350nm CWL, 40nm FWHM, 25mm Mounted Diameter



Stock **#67-825** ☐ In Stock

[Additional Bandwidths](#)

1

C\$371.00

ADD TO CART

Qty 1-9
C\$371.00
Qty 10+
C\$333.48
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 350.00 ±5
Center Wavelength CWL Tolerance (nm): ±5
Full Width-Half Max FWHM (nm): 40.00 ±8
Full Width-Half Max FWHM Tolerance (nm): ±8
Minimum Transmission (%): >25
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: General Filtering
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 4.9

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
