

35mm 2 MegaPixel Fixed Focal Length Lens



35mm Fixed Focal Length, #14-400

Stock **#14-400** ☐ In Stock

-

1

+

C\$441.00

ADD TO CART

Qty 1+

C\$441.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
36.91

Horizontal Field of View, 1/2" Sensor:
10.5°

Horizontal Field of View, 2/3" Sensor:
14.4°

Filter Thread:
M30.5 x0.50 (Female)

Maximum Diameter (mm): 32.5
Weight (g): 90
Horizontal Field of View, 1/3" Sensor: 8°
Maximum Image Circle (mm): 11.00
Horizontal Field of View @ Max Sensor Format: 14.4°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 35.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 500 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/32
Distortion (%): <-1
Horizontal Field of View, 1/4" Sensor: 5.23°
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View