

TECHSPEC® 3.5mm, f/4 Cr Series Fixed Focal Length Lens



3.5mm Cr Series Fixed Focal Length Lens

Stock **#37-394** ☐ In Stock

1 **C\$847.00**

ADD TO CART

Qty 1+

C\$847.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Fixed

Length (mm):
39.01

Horizontal Field of View, 1/2" Sensor:
29.5mm - 87.2°

Filter Thread:
M105 x 1.00 with required adapter [#89-848](#)

Weight (g):
120

Horizontal Field of View, 1/3" Sensor: 23.0mm - 74.4°
Maximum Image Circle (mm): 9.00
Horizontal Field of View @ Max Sensor Format: 41.2mm - 102.8°
Number of Elements (Groups): 8 (7)
Horizontal Field of View, 1/1.8" Sensor: 41.2mm - 102.8°
Front Thread: M50.0 x0.5 (Male)
Type: Fixed Focal Length Lens
Diameter (mm): 33.80
Focal Length FL (mm): 3.50
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 0 - ∞
Mount: C-Mount
Aperture (f/#): f/4
Coating: 425 - 675nm BBAR
Horizontal Field of View, 1/4" Sensor: 16.3mm - 57.4°
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View