

35mm Fixed Focal Length Lens



#86-210



Stock **#86-209** [CONTACT US](#)

- 1 + C\$2,779⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$2,779.00 each
Need More?	Request Quote

Product Downloads

General

Product Family:
4/3" Format Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

74.00	Length (mm):
45.0	Maximum Diameter (mm):
45	Outer Diameter (mm):
210.00	Weight (g):

Optical Properties

29.6	Horizontal Field of View @ Max Sensor Format:
100.00	Field of View @ Min Working Distance (mm):
21.60	Maximum Image Circle (mm):
35.00	Focal Length FL (mm):
200 - ∞	Working Distance (mm):
f/2 - f/16	Aperture (f/#):
<-0.2	Distortion (%):
-0.17	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor

4/3"	Maximum Sensor Format:
5.00	Pixel Size (µm):

Threading & Mounting

M37.5 x 0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TV Distortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.