

3600 Grooves/mm, 12.7mm Square, UV Holographic Grating



Reflective Holographic Gratings

Stock **#43-778** ☐ In Stock

-

1

+

C\$142.80

ADD TO CART

Qty 1+

C\$142.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
3600

Wavelength Range (nm):
250 - 400

Dimensions (mm):
12.7 x 12.7 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 12.70
Substrate:  Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 56
Peak Efficiency Avg, Typical (%): >39

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
