

TECHSPEC® 12.5mm Dia. x 25.0mm FL, Uncoated, Plano-Convex Lens



Stock **#37-789** ☐ In Stock
[Other Coating Options](#)

1 **C\$39.20**

ADD TO CART

Qty 1-9
C\$39.20
Qty 10+
C\$35.35
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Back Focal Length BFL (mm): 22.96
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.10 ±0.05
Edge Thickness ET (mm): 1.49
Radius R₁ (mm): 12.92
Clear Aperture CA (mm): 11.5
f#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View