

## 38.1mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock **#47-115** ☐ In Stock

1  **C\$294.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$294.00                     |
| Qty 6+                        |
| C\$264.60                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Diameter (mm):  
38.10 +0.00/-0.38

Substrate: ☐  
Aluminum 6061-T6

Surface Quality:  
80-50

Coating Specification:

R<sub>avg</sub> >85% @ 400 - 700nm  
R<sub>avg</sub> >70% @ 700 - 2000nm  
R<sub>avg</sub> >97% @ 2 - 12μm

**Coating:**  
Protected Aluminum (400-12000nm)

**Coating Type:**  
Metal

**Clear Aperture (%):**  
90

**Mounting Threads:**  
6-32 TPI Tapped Holes

**Surface Roughness (Angstroms):**  
<175

**Thickness (mm):**  
9.50

**Type:**  
Flat Mirror

**Wavelength Range (μm):**  
0.4 - 12

**Wavelength Range (nm):**  
400 - 12000

**Surface Flatness (RMS):**  
λ/4

Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 235:**  
[Compliant](#)