

38.1mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#69-247** ☐ In Stock

1

C\$34.30

ADD TO CART

Qty 1-5

C\$34.30

Qty 6+

C\$27.30

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
38.10 ±0.76

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:

80-50
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 3.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant