

38.4mm Diameter x 30mm FL, PCX Condenser Lens



Stock **#43-594** ☐ In Stock

[Other Coating Options](#)



1



C\$63.00

ADD TO CART

Qty 1-10

C\$63.00

Qty 11+

C\$56.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
38.40 +0.2/-0.4

Effective Focal Length EFL (mm):
30.00

Numerical Aperture NA:
0.64

Substrate: ☐

[B270](#)

Focal Length Tolerance (%):
±7

Coating:
Uncoated

Centering (arcmin):
≤25

Surface Quality:
80-50 (typical)

Center Thickness CT (mm):
19.00 ±0.25

f/#:
0.78

Bevel:
Protective bevel as needed

Radius R₂ (mm):
84.125

Shape of Back Surface:
Convex

Type:
Condenser Lens

Wavelength Range (nm):
350 - 2500

Conjugate Distance:
Infinite

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)