

## 3μm λ/2 MWIR Zero Order Waveplate



Stock **#85-117** [CONTACT US](#)

- 1 + **C\$1,302.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$1,302.00                   |
| Qty 10+                       |
| C\$1,183.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Clear Aperture CA (mm):  
10.0

Design Wavelength DWL (nm):  
3000

Diameter (mm):  
25.40

Substrate: ☐  
MgF<sub>2</sub>

|                                                      |
|------------------------------------------------------|
| <b>Retardance:</b><br>λ/2                            |
| <b>Type:</b><br>Crystalline Waveplate                |
| <b>Parallelism (arcmin):</b><br>3                    |
| <b>Construction:</b><br>Crystalline                  |
| <b>Transmitted Wavefront, P-V:</b><br><λ/8 @ 632.8nm |
| <b>Retardance Tolerance:</b><br>λ/100 @ 20°C         |
| <b>Mount Thickness (mm):</b><br>6.0                  |
| <b>Retardance Order:</b><br>0                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |