

TECHSPEC®

3" Dia, 6" FL Enhanced Alum., Spherical Mirror



Stock #43-556 ☐ In Stock

-

1

+

C\$378.00

ADD TO CART

Qty 1-9
C\$378.00
Qty 10+
C\$321.30
Volume Pricing
Request Quote

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy:

N4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 6.00
Effective Focal Length EFL (mm): 152.40
Radius of Curvature (mm): 304.80
Aperture (f/#): f/2
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant