


TECHSPEC® 3X, UV Enhanced Aluminum Canopus® Reflective Beam Expander



TECHSPEC® Canopus™ Reflective Beam Expanders



Stock **#37-186** ☐ In Stock

- 1 +

C\$826.00

ADD TO CART

Qty 1-5

C\$826.00

Qty 6+

C\$729.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Enhanced Aluminum (250-700nm)

Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 4
Exit Aperture (mm): 12
Expansion Power: 3X
Substrate: Aluminum 6061-T6
Height (mm): 25.4
Length (mm): 72.60
Surface Quality: 40-20
Type: Beam Expander
Weight (g): 117
Width (mm): 38.10
Coating Specification: R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm
Wavelength Range (nm): 250 - 700
Style: Fixed Magnification
Surface Roughness (Angstroms): <50 RMS
Wavefront Error, P-V: ≤λ/10 on-axis for a 1mm Dia. Input Beam

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View