

[See all 21 Products in Family](#)

4-10mm FL, C-Mount, P-Iris, IR Cut Standard Lens



Image represents #22-825; Design will vary by stock number.



Stock **#22-818** 1 In Stock

-

1

+

C\$1,064⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,064.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Varifocal Lens

Type:

Physical & Mechanical Properties

P-iris

Iris Option:

51.50	Length (mm):
Not Specified	Maximum Diameter (mm):
78	Weight (g):

Optical Properties

112 - 44	Horizontal Field of View @ Max Sensor Format:
4-10	Focal Length Range (mm):
Not Specified	Working Distance (mm):
F/1.4 to closed	Aperture (f/#):
VS	Lens Wavelength Range:

Sensor

1/1.7"	Maximum Sensor Format:
--------	------------------------

Threading & Mounting

C-Mount	Mount:
---------	--------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
 - True 4K, 12 Megapixel Resolution
 - IR corrected for Day or Night
- 4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.