

[See all 21 Products in Family](#)

4-10mm FL CS-Mount, DC Auto Iris, IR Corrected Lens



Image represents #22-799; Design will vary by stock number.

Stock **#22-799** **1 In Stock**

-

1

+

C\$656⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$656.60 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
Varifocal Lens	Type:
Physical & Mechanical Properties	
DC Auto Iris	Iris Option:
51.50	Length (mm):

59.0	Maximum Diameter (mm):
78	Weight (g):
Optical Properties	
112° - 44°	Horizontal Field of View @ Max Sensor Format:
4-10	Focal Length Range (mm):
500 - ∞	Working Distance (mm):
f/1.4 - Closed	Aperture (f/#):
VIS	Lens Wavelength Range:
Sensor	
1/1.7"	Maximum Sensor Format:
Threading & Mounting	
CS-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.