

4-10mm FL, CS-Mount, P-iris, 4K Ultra Motorized with Limit Switch



Image represents #22-806: Design will vary by stock number.

Stock **#22-808** ☐ In Stock

-

1

+

C\$616.00

ADD TO CART

Qty 1+

C\$616.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Precise Iris

Length (mm):
51.50

Maximum Diameter (mm):
59.0

Weight (g):
77

Horizontal Field of View @ Max Sensor Format: 112° - 44°
Note: User with Motorized Lens Control Board (#22-832)
Type: Varifocal Lens
Maximum Sensor Format: 1/1.7"
Working Distance (mm): 500 - ∞
Mount: CS-Mount
Aperture (f/#): f/1.4 - Closed
Lens Wavelength Range: VS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View