

4" LED Ring Light White with Barrel Mount

See More by [Advanced Illumination](#)



Stock **#66-779** [CONTACT US](#)

- 1 + **C\$1,209.60**

ADD TO CART

Qty 1+
C\$1,209.60

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: White
Diameter (mm): 100.00
Height (mm): 33.8
Inner Diameter (mm): 55.5

Model Number: RL4260B-WHHC
Mount: Barrel Mount
Operating Temperature (°C): 0 to 65
Dimensions (mm): 100 Dia x33.8 T
Mounting Threads: M4 x4
Working Distance (inches): 4.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%) : ±10 edge to edge (dependent on working distance)
Number of LEDs: 60.00
Number of Channels: 1.00
Field Coverage (mm): 43.18 (1.7 inches)
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)