

4-Screw Model, Laser Bezel Plate



4-Screw Model, Laser Bezel Plate, #61-344

Stock **#61-344** **10 In Stock**

⊖ 1 ⊕ C\$345⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$345.80 each
Need More?	Request Quote

Product Downloads



General

Note:
Fits JDS Uniphase Cylinder Head Models with 1.740" Diameters

Compatible Laser Stock Number:
[#62-720](#), [#62-721](#), [#62-723](#), [#62-724](#), [#62-725](#), [#62-726](#), [#62-727](#), [#62-728](#), [#62-729](#), [#62-731](#), [#62-732](#)

Regulatory Compliance

[Compliant](#)

RoHS 2015:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

