

4 Watt, 115V, 365nm UV Curing Lamp



4 Watt, 115V, 365nm UV Curing Lamp, #86-800

Stock **#86-800** [CONTACT US](#)

-

1

+

C\$361²⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$361.20 each
Need More?	Request Quote

Product Downloads

Optical Properties

	Wavelength (nm):
365.00	
	Irradiance at 76.2mm (μW/cm²):
1000	

Hardware & Interface Connectivity

	Power Requirement:
4W, 115V	

Regulatory Compliance

Product Details

Stands are not included, but recommended for hands free curing or analysis.

- 4-Watt and 6-Watt Models Centered at 365nm
- Stands are Available for Hands Free Curing
- Portable, High Intensity Design

Handheld UV Curing Lamps are portable benchtop lamps designed for a variety of applications including the fluorescence of stained gels, sterilization, or UV curing. These lamps feature ergonomically designed handles with conveniently placed on/off switches. These lamps are portable, with a high-intensity design. Handheld UV Curing Lamps are ideal for quickly curing Edmund Optics' full line of [Norland Optical Adhesives](#). These lamps are available in 4-watt and 6-watt models centered at 365nm.

Note: Stands are not included, but are recommended for hands free curing or analysis.